



A portable unit designed for facilitating communication between a speaker and wearer/s of T-coil hearing aids. The LoopHEAR™ is ideal for one to one applications such as at service counters, railway stations, banks, in vehicles and at small meeting rooms. This lightweight unit includes, within the casing an induction loop and a built-in amplifier.

The LH102 V2 complies with EN60118-4.

FEATURES

- ➔ Portable Loop with fixed option
- ➔ Magnetic field strength LED indicator
- ➔ Built-in microphone
- ➔ 3.5 mm Connection for audio Equipment (MP3, computer, etc)
- ➔ Low battery + recharging LED indicators
- ➔ On/Off switch
- ➔ Induction Loop Functioning Indicator
- ➔ Adjusting the input level
- ➔ Adjustable magnetic field
- ➔ Adjustable tone control
- ➔ Supplied in a lightweight case

- Key benefit of the LH102 V2 LT:

- ✓ Connector for an external Loop



ACCESSORIES INCLUDED

- ➔ Rechargeable Batteries 9xAAA (1,2V / 800mA)
- ➔ External power supply adaptor 230VAC - 15VDC
- ➔ Theft Preventing Desk Mounting Plate
- ➔ Official symbol of "crossed ear" for the signage

TECHNICAL SPECIFICATIONS

- ➔ Range of 1m²
Possibility of connecting an external loop to cover a larger area (30 to 50m²).
- ➔ Battery time:
 - 5 to 7 hours when fully charged
 - Standby (when turned on but not in use): 1 Day
 - Standby (when turned off) : 4 months
- ➔ Power supply (UK, VDE or US)
- ➔ Weight: 750 g
- ➔ Size: 25 x 22 x 7 cm

OPTIONAL (Included in the LH-102 V2)

- ➔ External Microphone with stand (3.5mm jack MIC connection and 2.1m cord)
- ➔ External HAC Ear Piece for private listening and its support